


CREST125

Open Flow Pumps




DAEPUMPS.COM

info@daepumps.com

(760) 821-8112

CREST125

Data Sheet




*Intermittent use : minimum one hour stop after 2 hours run / *Occasional use : maximum one hour a day

SHOE SHIMMING TABLE - CREST125		
Pressure psi (bar)	Speed - Rpm	Number of shims* - thickness 0.019 in (0.5 mm)
$\Delta P \leq 72.5$ (5)	0 to 10	0
	10 to 35	0
72.5 (5) $\leq \Delta P \leq 108.75$ (7.5)	0 to 10	2
	10 to 27.5	1
108.75 (7.5) $\leq \Delta P \leq 145$ (10)	0 to 10	3
	10 to 25	2
145 (10) $\leq \Delta P \leq 217.5$ (15)	0 to 10	4
	10 to 20	3

*Remove one shim if temperature exceeds 140° Fahrenheit (60° Celsius)

DIMENSIONS



TYPE	A	B	C	D	E	F	G	H	I	J	K	L	M	N	O	P	Q
CREST125	101.2 (258.5)	50.1 (1273)	40.8 (1037)	32.2 (818)	67.5 (1715)	39.4 (1000)	45.7 (1160)	19.7 (500)	74.8 (1900)	78.7 (2000)	4xø1.0 (4xø27)	6.3 (160.5)	5.7 (144.5)	ANSI 5 in / 150# DN125 PN16	14.3 (363.5)	19.7 (500)	